







Placca Gira Esprit alluminio (anodizzato)



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----|-----------------------|----|---------------|
|  1 modulo | 0211 17 | 1 | 45,80 | 11 | 4010337211174 |
|  1,5 moduli | 1001 17 | 1 | 67,94 | 11 | 4010337881513 |
|  2 moduli | 0212 17 | 1 | 78,33 | 11 | 4010337212171 |
|  2 moduli senza costola centrale | 1002 17 | 1 | 78,33 | 11 | 4010337002178 |
|  3 moduli | 0213 17 | 1 | 130,60 | 11 | 4010337213178 |
|  4 moduli | 0214 17 | 1 | 180,39 | 11 | 4010337214175 |

Caratteristiche

- Alluminio anodizzato E 1 EV 1.