

**Placca Gira F100
bianco puro brillante**



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|-----|-----------------------|----|---------------|
|  1 modulo | 0211 112 | 10 | 7,80 | 01 | 4010337043973 |
|  2 moduli | 0212 112 | 10 | 13,77 | 01 | 4010337044017 |
|  2 moduli senza costola centrale | 1002 112 | 10 | 13,77 | 01 | 4010337047094 |
|  3 moduli | 0213 112 | 1/5 | 22,23 | 01 | 4010337044031 |
|  4 moduli | 0214 112 | 1/5 | 35,78 | 01 | 4010337044055 |
|  5 moduli | 0215 112 | 1/5 | 54,65 | 01 | 4010337044079 |

Caratteristiche

- Infrangibile.

Avvisi

- In combinazione con la flangia di tenuta, adatta anche per il montaggio da incasso IP44 (protezione dall'acqua).