









Copertura cieca con anello portante



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|--------|-----------------------|----|---------------|
|  bianco crema brillante | 0268 01 | 10 | 11,83 | 01 | 4010337268017 |
|  bianco puro brillante | 0268 03 | 10/100 | 11,83 | 01 | 4010337268031 |
|  bianco puro satinato | 0268 27 | 10 | 11,83 | 01 | 4010337268277 |
|  antracite | 0268 28 | 10 | 14,58 | 11 | 4010337268284 |
|  color alluminio | 0268 26 | 10 | 18,71 | 11 | 4010337268260 |
|  nero opaco | 0268 005 | 10 | 18,71 | 11 | 4010337037040 |
|  grigio opaco | 0268 015 | 10 | 18,71 | 11 | 4010337078487 |
|  acciaio inox | 0268 600 | 5 | 22,75 | 11 | 4010337021865 |

Avvisi

- Solo per fissaggio a viti.