










Copertura cieca con anello portante



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0268 01	10	11,46	01	4010337268017
 bianco puro brillante	0268 03	10/100	11,46	01	4010337268031
 bianco puro satinato	0268 27	10	11,46	01	4010337268277
 antracite	0268 28	10	14,13	11	4010337268284
 color alluminio	0268 26	10	18,13	11	4010337268260
 nero opaco	0268 005	10	18,13	11	4010337037040
 grigio opaco	0268 015	10	18,13	11	4010337078487
 acciaio inox	0268 600	5	22,04	11	4010337021865

Avvisi

- Solo per fissaggio a viti.