







Presse altoparlante stereo



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0402 01	1/5	18,71	01	4010337402015
 bianco puro brillante	0402 03	1/5	18,71	01	4010337402039
 bianco puro satinato	0402 27	1/5	18,71	01	4010337402275
 antracite	0402 28	1/5	21,31	11	4010337402282
 color alluminio	0402 26	1/5	23,96	11	4010337402268
 nero opaco	0402 005	1/5	23,96	11	4010337037880

Caratteristiche

- Con morsetti a vite.

Dati tecnici

Profondità di montaggio: 31 mm

Sezione dei conduttori max.: 1,5mm²

Avvisi

- Per conduttori di sezione fino a max 10 mm².
 - Utilizzo con funzione di modulo per connettore a spina per altoparlante high-end (WBT) e calotta dati.
-