







## Presse equipotenziale, 2 moduli



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0405 01	1/5	39,20	01	4010337405016
 bianco puro brillante	0405 03	1/5	39,20	01	4010337405030
 bianco puro satinato	0405 27	1/5	39,20	01	4010337405276
 antracite	0405 28	1/5	41,79	11	4010337405283
 color alluminio	0405 26	1/5	45,86	11	4010337405269
 nero opaco	0405 005	1/5	45,86	11	4010337037316

### Caratteristiche

- Per collegare degli strumenti medici. DIN 42 801.

### Dati tecnici

Profondità di montaggio: 31 mm  
Sezione dei conduttori: 6 - 10 mm<sup>2</sup>