









## Coperchio con manopola per dimmer e potenziometro elettronico



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0650 01	10	6,71	02	4010337650010
 bianco puro brillante	0650 03	10/100	6,71	02	4010337650034
 bianco puro satinato	0650 27	10	6,71	02	4010337650270
 antracite	0650 28	10	10,07	02	4010337650287
 color alluminio	0650 26	10	15,30	02	4010337650263
 nero opaco	0650 005	10	15,30	02	4010337036593
 grigio opaco	0650 015	10	15,30	02	4010337081210
 acciaio inox	0650 600	1	21,40	02	4010337022329