








## Copertura con traversina per temporizzatore e interruttore o pulsante per veneziane



| Specifica   | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN           |
|---|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante  | 0666 01   | 5  | 9,00                  | 01 | 4010337666011 |
|  bianco puro brillante | 0666 03   | 5  | 9,00                  | 01 | 4010337666035 |
|  bianco puro satinato  | 0666 27   | 5  | 9,00                  | 01 | 4010337666271 |
|  antracite             | 0666 28   | 5  | 13,01                 | 11 | 4010337666288 |
|  color alluminio       | 0666 26   | 5  | 19,12                 | 11 | 4010337666264 |
|  nero opaco            | 0666 005  | 5  | 19,12                 | 11 | 4010337036586 |
|  grigio opaco          | 0666 015  | 5  | 19,12                 | 11 | 4010337081401 |

### Avvisi

- Sostituendo i vetri con i simboli per veneziana e tempo, questa copertura è di impiego universale.

## Contenuto della fornitura

- I vetri con i simboli per veneziana ( $\Delta$ ,  $\nabla$ ) e tempo (da 15 a 120 min o da 30 a 60 min) sono in dotazione.

---