








Copertura con traversina per temporizzatore e interruttore o pulsante per veneziane



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante | 0666 01 | 5 | 8,67 | 01 | 4010337666011 |
|  bianco puro brillante | 0666 03 | 5 | 8,67 | 01 | 4010337666035 |
|  bianco puro satinato | 0666 27 | 5 | 8,67 | 01 | 4010337666271 |
|  antracite | 0666 28 | 5 | 12,53 | 11 | 4010337666288 |
|  color alluminio | 0666 26 | 5 | 18,42 | 11 | 4010337666264 |
|  nero opaco | 0666 005 | 5 | 18,42 | 11 | 4010337036586 |
|  grigio opaco | 0666 015 | 5 | 18,42 | 11 | 4010337081401 |

Avvisi

- Sostituendo i vetri con i simboli per veneziana e tempo, questa copertura è di impiego universale.

Contenuto della fornitura

- I vetri con i simboli per veneziana (,) e tempo (da 15 a 120 min o da 30 a 60 min) sono in dotazione.
