









## Copertura per presa coassiale per antenna



| Specifica   | Cod. ord. | UI     | EUR/pezzo IVA esclusa | SP | EAN           |
|---|-----------|--------|-----------------------|----|---------------|
|  bianco crema brillante  | 0869 01   | 10/100 | 6,02                  | 01 | 4010337869016 |
|  bianco puro brillante | 0869 03   | 10/100 | 6,02                  | 01 | 4010337009504 |
|  bianco puro satinato  | 0869 27   | 10/100 | 6,02                  | 01 | 4010337869276 |
|  antracite             | 0869 28   | 10     | 8,55                  | 11 | 4010337869283 |
|  color alluminio       | 0869 26   | 10     | 12,43                 | 11 | 4010337869269 |
|  nero opaco            | 0869 005  | 10     | 12,43                 | 11 | 4010337036616 |
|  grigio opaco          | 0869 015  | 10     | 12,43                 | 11 | 4010337081890 |
|  acciaio inox          | 0869 600  | 5      | 16,12                 | 11 | 4010337021605 |

## Caratteristiche

- Terzo foro rompibile.

---

## Avvisi

- Solo per fissaggio con viti.

---