










Copertura per presa coassiale per antenna



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0869 01	10/100	6,28	01	4010337869016
 bianco puro brillante	0869 03	10/100	6,28	01	4010337009504
 bianco puro satinato	0869 27	10/100	6,28	01	4010337869276
 antracite	0869 28	10	8,93	11	4010337869283
 color alluminio	0869 26	10	12,98	11	4010337869269
 nero opaco	0869 005	10	12,98	11	4010337036616
 grigio opaco	0869 015	10	12,98	11	4010337081890
 acciaio inox	0869 600	5	16,83	11	4010337021605

Caratteristiche

- Terzo foro rompibile.

Avvisi

- Solo per fissaggio a viti.
