

**Placca Gira E2
antracite**



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|--------|-----------------------|----|---------------|
|  1 modulo | 0211 23 | 10/100 | 8,16 | 11 | 4010337211235 |
|  1,5 moduli | 1001 23 | 10 | 12,02 | 11 | 4010337881339 |
|  2 moduli | 0212 23 | 10/100 | 11,79 | 11 | 4010337212232 |
|  2 moduli senza costola centrale | 1002 23 | 10 | 11,79 | 11 | 4010337002239 |
|  3 moduli | 0213 23 | 1/5 | 20,42 | 11 | 4010337213239 |
|  4 moduli | 0214 23 | 1/5 | 32,89 | 11 | 4010337214236 |
|  5 moduli | 0215 23 | 1/5 | 50,15 | 11 | 4010337215233 |

Caratteristiche

- Plastica: materiale termoplastico privo di alogen, resistente agli urti e infrangibile

Avvisi

- Adatta anche per installazioni in canalina.
 - Placca (1 - 5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.
-