











## Copertura con schermo innestabile per rilevatore di movimento 1,10 m Standard



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	1470 01	1	5,10	02	4010337020967
 bianco puro brillante	1470 03	1	5,10	02	4010337020974
 color alluminio	1470 26	1	13,55	02	4010337030010
 bianco puro satinato	1470 27	1	5,10	02	4010337075257
 antracite	1470 28	1	8,44	02	4010337075264
 grigio	1470 42	1	10,11	02	4010337075295
 color alluminio	1470 65	1	31,52	02	4010337075516
 bianco puro	1470 66	1	23,03	02	4010337075523
 antracite	1470 67	1	31,52	02	4010337075530

	bianco puro brillante	1470 112	1	8,65	02	4010337075240
---	-----------------------	----------	---	------	----	---------------

---

	bianco puro	1470 40	1	10,11	02	4010337075271
---	-------------	---------	---	-------	----	---------------

---