









## Set di interruttori a bilico 1 modulo



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante (verniciato)	2181 01	1	13,98	06	4010337012061
 bianco puro brillante (verniciato)	2181 03	1	13,98	06	4010337012078
 bianco puro satinato (verniciato)	2181 27	1	13,98	06	4010337013365
 antracite (verniciato)	2181 28	1	17,39	06	4010337012085
 color alluminio (verniciato)	2181 26	1	21,24	06	4010337012108
 nero opaco (verniciato)	2181 005	1	21,24	06	4010337038290
 grigio opaco (verniciato)	2181 015	1	21,24	06	4010337083153
 acciaio inox	2131 601	1	15,69	06	4010337019978

### Avvisi

- I set di interruttori a bilanciare scrivibili e i set di interruttori a bilanciare senza campo per targhetta sono realizzati in metallo: in caso di applicazioni a radiofrequenza la portata può risultare ridotta.