









Set di interruttori a bilico 2 moduli (1+1)



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante (verniciato)	2182 01	1	23,32	06	4010337012092
 bianco puro brillante (verniciato)	2182 03	1	23,32	06	4010337012115
 bianco puro satinato (verniciato)	2182 27	1	23,32	06	4010337013372
 antracite (verniciato)	2182 28	1	26,72	06	4010337012139
 color alluminio (verniciato)	2182 26	1	30,56	06	4010337012122
 nero opaco (verniciato)	2182 005	1	30,56	06	4010337038320
 grigio opaco (verniciato)	2182 015	1	30,56	06	4010337083160
 acciaio inox	2132 601	1	21,42	06	4010337020059

Avvisi

- I set di interruttori a bilanciere scrivibili e i set di interruttori a bilanciere senza campo per targhetta sono realizzati in metallo: in caso di applicazioni a radiofrequenza la portata può risultare ridotta.