











Set di interruttori a bilico 3 moduli



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante (verniciato)	2183 01	1	30,26	06	4010337012146
 bianco puro brillante (verniciato)	2183 03	1	30,26	06	4010337012153
 bianco puro satinato (verniciato)	2183 27	1	30,26	06	4010337013389
 antracite (verniciato)	2183 28	1	34,33	06	4010337012160
 colore alluminio (verniciato)	2183 26	1	37,36	06	4010337012177
 nero opaco (verniciato)	2183 005	1	37,36	06	4010337038382
 grigio opaco (verniciato)	2183 015	1	37,36	06	4010337083177
 acciaio inox	2133 601	1	25,11	06	4010337020196
 bronzo	2133 605	1	24,38	06	4010337083399

Avvisi

- I set di interruttori a bilanciere scrivibili e i set di interruttori a bilanciere senza campo per targhetta sono realizzati in metallo: in caso di applicazioni a radiofrequenza la portata può risultare ridotta.
