











Set di interruttori a bilico 4 moduli (1+3)



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante (verniciato)	2184 01	1	37,80	06	4010337012184
 bianco puro brillante (verniciato)	2184 03	1	37,80	06	4010337012191
 bianco puro satinato (verniciato)	2184 27	1	37,80	06	4010337013396
 antracite (verniciato)	2184 28	1	41,11	06	4010337012207
 colore alluminio (verniciato)	2184 26	1	44,87	06	4010337012214
 nero opaco (verniciato)	2184 005	1	44,87	06	4010337038412
 grigio opaco (verniciato)	2184 015	1	44,87	06	4010337083474
 acciaio inox	2134 601	1	27,88	06	4010337020226
 bronzo	2134 605	1	27,07	06	4010337083481

Avvisi

- I set di interruttori a bilanciere scrivibili e i set di interruttori a bilanciere senza campo per targhetta sono realizzati in metallo; in caso di applicazioni a radiofrequenza la portata può risultare ridotta.
