










Set di interruttori a bilico 2 moduli Plus



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante (verniciato)	2192 01	1	30,99	06	4010337012269
 bianco puro brillante (verniciato)	2192 03	1	30,99	06	4010337012276
 bianco puro satinato (verniciato)	2192 27	1	30,99	06	4010337013419
 antracite (verniciato)	2192 28	1	35,15	06	4010337012283
 color alluminio (verniciato)	2192 26	1	38,26	06	4010337012290
 nero opaco (verniciato)	2192 005	1	38,26	06	4010337038351
 grigio opaco (verniciato)	2192 015	1	38,26	06	4010337083832
 acciaio inox	2142 601	1	25,71	06	4010337020141

Avvisi

- I set di interruttori a bilanciere scrivibili e i set di interruttori a bilanciere senza campo per targhetta sono realizzati in metallo: in caso di applicazioni a radiofrequenza la portata può risultare ridotta.