









Set di interruttori a bilico 5 moduli Plus (2+3)



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante (verniciato)	2195 01	1	57,68	06	4010337012313
 bianco puro brillante (verniciato)	2195 03	1	57,68	06	4010337012320
 bianco puro satinato (verniciato)	2195 27	1	57,68	06	4010337013426
 antracite (verniciato)	2195 28	1	68,39	06	4010337012337
 color alluminio (verniciato)	2195 26	1	76,27	06	4010337012344
 nero opaco (verniciato)	2195 005	1	76,27	06	4010337038443
 grigio opaco (verniciato)	2195 015	1	76,27	06	4010337083849
 acciaio inox	2145 601	1	40,00	06	4010337020295

Avvisi

- I set di interruttori a bilanciere scrivibili e i set di interruttori a bilanciere senza campo per targhetta sono realizzati in metallo: in caso di applicazioni a radiofrequenza la portata può risultare ridotta.