










Set di interruttori a bilico 5 moduli Plus (2+3)



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|--|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante (verniciato) | 2195 01 | 1 | 57,68 | 06 | 4010337012313 |
|  bianco puro brillante (verniciato) | 2195 03 | 1 | 57,68 | 06 | 4010337012320 |
|  bianco puro satinato (verniciato) | 2195 27 | 1 | 57,68 | 06 | 4010337013426 |
|  antracite (verniciato) | 2195 28 | 1 | 68,39 | 06 | 4010337012337 |
|  color alluminio (verniciato) | 2195 26 | 1 | 76,27 | 06 | 4010337012344 |
|  nero opaco (verniciato) | 2195 005 | 1 | 76,27 | 06 | 4010337038443 |
|  grigio opaco (verniciato) | 2195 015 | 1 | 76,27 | 06 | 4010337083849 |
|  acciaio inox | 2145 601 | 1 | 40,00 | 06 | 4010337020295 |
|  bronzo | 2145 605 | 1 | 38,82 | 06 | 4010337083726 |

Avvisi

- I set di interruttori a bilanciere scrivibili e i set di interruttori a bilanciere senza campo per targhetta sono realizzati in metallo: in caso di applicazioni a radiofrequenza la portata può risultare ridotta.
