











## Altoparlante radio da incasso



| Specifica   | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN           |
|---|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante  | 2282 01   | 1  | 26,73                 | 03 | 4010337076230 |
|  bianco puro brillante | 2282 03   | 1  | 26,73                 | 03 | 4010337076247 |
|  bianco puro satinato  | 2282 27   | 1  | 26,73                 | 03 | 4010337076254 |
|  antracite             | 2282 28   | 1  | 28,78                 | 03 | 4010337076261 |
|  color alluminio       | 2282 26   | 1  | 31,35                 | 03 | 4010337076162 |
|  aspetto in vetro nero | 2282 05   | 1  | 35,98                 | 03 | 4010337889182 |
|  nero opaco            | 2282 005  | 1  | 31,35                 | 03 | 4010337037286 |
|  grigio opaco          | 2282 015  | 1  | 31,35                 | 03 | 4010337083931 |
|  acciaio inox          | 2282 600  | 1  | 35,98                 | 03 | 4010337032861 |

## Caratteristiche

- Altoparlante da collegare alla radio da incasso Gira.

---

## Dati tecnici

|   |                    |
|---|--------------------|
| Profondità di montaggio:                                    | 32 mm              |
| Sezione dei conduttori<br>- Allacciamento altoparlante/AUX: | 1,5mm <sup>2</sup> |
| Impedenza:  | 8 Ω                |
| Temperatura ambiente:                                       | da -5 °C a +50 °C  |

---