











Altoparlante radio da incasso



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2282 01	1	26,73	03	4010337076230
 bianco puro brillante	2282 03	1	26,73	03	4010337076247
 bianco puro satinato	2282 27	1	26,73	03	4010337076254
 antracite	2282 28	1	28,78	03	4010337076261
 color alluminio	2282 26	1	31,35	03	4010337076162
 aspetto in vetro nero	2282 05	1	35,98	03	4010337889182
 nero opaco	2282 005	1	31,35	03	4010337037286
 grigio opaco	2282 015	1	31,35	03	4010337083931
 acciaio inox	2282 600	1	35,98	03	4010337032861

Caratteristiche

- Altoparlante da collegare alla radio da incasso Gira.

Dati tecnici

Profondità di montaggio:	32 mm
Sezione dei conduttori - Allacciamento altoparlante/AUX:	1,5mm ²
Impedenza:	8 Ω
Temperatura ambiente:	da -5 °C a +50 °C
