









## Copertura con uscita inclinata a 30° e campo per targhetta per anello portante Modular Jack 2 moduli



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2640 01	10	8,56	01	4010337460114
 bianco puro brillante	2640 03	10	8,56	01	4010337460138
 bianco puro satinato	2640 27	10	8,56	01	4010337460183
 antracite	2640 28	10	11,30	11	4010337460190
 color alluminio	2640 26	10	15,43	11	4010337460176
 nero opaco	2640 005	10	15,43	11	4010337036500
 grigio opaco	2640 015	10	15,43	11	4010337085195
 acciaio inox	2640 600	10	19,43	11	4010337021582

### Contenuto della fornitura

- Targhetta delle diciture in bianco in dotazione.