









Copertura con uscita inclinata a 30° e campo per targhetta per anello portante Modular Jack 2 moduli



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante | 2640 01 | 10 | 8,56 | 01 | 4010337460114 |
|  bianco puro brillante | 2640 03 | 10 | 8,56 | 01 | 4010337460138 |
|  bianco puro satinato | 2640 27 | 10 | 8,56 | 01 | 4010337460183 |
|  antracite | 2640 28 | 10 | 11,30 | 11 | 4010337460190 |
|  color alluminio | 2640 26 | 10 | 15,43 | 11 | 4010337460176 |
|  nero opaco | 2640 005 | 10 | 15,43 | 11 | 4010337036500 |
|  grigio opaco | 2640 015 | 10 | 15,43 | 11 | 4010337085195 |
|  acciaio inox | 2640 600 | 10 | 19,43 | 11 | 4010337021582 |

Contenuto della fornitura

- Targhetta delle diciture in bianco in dotazione.