










## Copertura per regolatore della temperatura ambiente con spia di controllo



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2702 01	10	10,55	02	4010337104377
 bianco puro brillante	2702 03	10	10,55	02	4010337104384
 bianco puro satinato	2702 27	10	10,55	02	4010337104315
 color alluminio	2702 26	10	17,10	02	4010337104353
 antracite	2702 28	10	12,06	02	4010337104360
 nero opaco	2702 005	10	17,10	02	4010337104346
 grigio opaco	2702 015	10	17,10	02	4010337104339
 acciaio inox	2702 600	10	17,10	02	4010337104308