








**Presse doppia SCHUKO 16 A 250 V~ con maggiore protezione contro i contatti accidentali (Safety Plus) per scatola da incasso 1,5 moduli**



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2735 01	10	20,83	01	4010337000822
 bianco puro brillante	2735 03	1	20,83	01	4010337771371
 bianco puro satinato	2735 27	1	20,83	01	4010337771555
 antracite	2735 28	1	23,35	11	4010337771364
 color alluminio	2735 26	1	27,23	11	4010337000785
 nero opaco	2735 005	10	27,23	11	4010337037521
 grigio opaco	2735 015	10	27,23	11	4010337085294

#### Dati tecnici

Profondità di montaggio:	25 mm
Sezione dei conduttori - per conduttori da:	da 1,5 mm <sup>2</sup> a 2,5 mm <sup>2</sup>
Altezza di montaggio:	6 mm

## Avvisi

- Maggiore protezione contro i contatti accidentali (Safety Plus) ai sensi della norma IEC 60884-1.

---