








**Presse SCHUKO 16 A 250 V~ con coperchio a cerniera, spia di controllo e shutter
System 55**

Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2763 01	1/5	32,26	01	4010337059448
 bianco puro brillante	2763 03	1/5	32,26	01	4010337059554
 bianco puro satinato	2763 27	1/5	32,26	01	4010337059578
 antracite	2763 28	1/5	33,42	11	4010337059585
 color alluminio	2763 26	1/5	37,61	11	4010337059561
 nero opaco	2763 005	1/5	37,61	11	4010337037613
 grigio opaco	2763 015	1/5	37,61	11	4010337085324

Dati tecniciProfondità di montaggio
- nuova generazione:

29 mm

Sezione dei conduttori
- per conduttori da:1,5 mm² a 2,5 mm²Temperatura ambiente
- shutter:

da 0 °C a -45 °C

Avvisi

- Maggiore protezione contro i contatti accidentali (Safety Plus) secondo IEC 60884-1.

Contenuto della fornitura

- L elemento di lampada al neon è in dotazione.
