








Presse per rasoio elettrico (DIN EN 61558 2-5) 115 - 230 V~ per placca 2 moduli senza costola centrale



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2820 01	1	112,84	29	4010337016755
 bianco puro brillante	2820 03	1	112,84	29	4010337016762
 antracite	2820 28	1	115,27	29	4010337016809
 color alluminio	2820 26	1	118,89	29	4010337016793
 nero opaco	2820 005	1	118,89	29	4010337037323
 grigio opaco	2820 015	1	118,89	29	4010337087090
 acciaio inox (verniciato)	2820 600	1	129,44	29	4010337021995