








Presse per rasoio elettrico (DIN EN 61558 2-5) 115 - 230 V~ per placca 2 moduli senza costola centrale



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante | 2820 01 | 1 | 112,84 | 29 | 4010337016755 |
|  bianco puro brillante | 2820 03 | 1 | 112,84 | 29 | 4010337016762 |
|  antracite | 2820 28 | 1 | 115,27 | 29 | 4010337016809 |
|  color alluminio | 2820 26 | 1 | 118,89 | 29 | 4010337016793 |
|  nero opaco | 2820 005 | 1 | 118,89 | 29 | 4010337037323 |
|  grigio opaco | 2820 015 | 1 | 118,89 | 29 | 4010337087090 |
|  acciaio inox (verniciato) | 2820 600 | 1 | 129,44 | 29 | 4010337021995 |