

Interruttore a bilanciere British Standard (BS EN 60669-1) 3 moduli con bilancieri Interruttore



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2830 01	10	24,06	29	4010337830016
 bianco puro brillante	2830 03	10	24,06	29	4010337830030
 antracite	2830 28	10	26,49	29	4010337830283
 color alluminio	2830 26	10	30,13	29	4010337830269
 nero opaco	2830 005	10	30,13	29	4010337038580
 grigio opaco	2830 015	10	30,13	29	4010337087113
 acciaio inox (verniciato)	2830 600	10	33,51	29	4010337022022

Dati tecnici

Profondità di montaggio:	25 mm
Sezione dei conduttori - per conduttori fino a:	2,5mm ²
Potenza nominale:	Carico LED 100 W (IEC 60669)