








## Interruttore a bilanciere British Standard (BS EN 60669-1) 3 moduli con bilancieri Deviatore universale



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2832 01	10	34,09	29	4010337832010
 bianco puro brillante	2832 03	10	34,09	29	4010337832034
 antracite	2832 28	10	36,64	29	4010337832287
 color alluminio	2832 26	10	40,53	29	4010337832263
 nero opaco	2832 005	10	40,53	11	4010337038528
 grigio opaco	2832 015	10	40,53	11	4010337087120
 acciaio inox (verniciato)	2832 600	10	44,15	29	4010337022053

### Caratteristiche

- Con morsetti a vite.

## Dati tecnici

Profondità di montaggio: 25 mm

Sezione dei conduttori  
- per conduttori fino a: 2,5mm<sup>2</sup>

---

## Avvisi

- Solo per fissaggio a viti.

---