







Interruttore a bilanciere British Standard (BS EN 60669-1) 3 moduli con bilancieri Deviatore universale



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante | 2832 01 | 10 | 34,09 | 29 | 4010337832010 |
|  bianco puro brillante | 2832 03 | 10 | 34,09 | 29 | 4010337832034 |
|  antracite | 2832 28 | 10 | 36,64 | 29 | 4010337832287 |
|  color alluminio | 2832 26 | 10 | 40,53 | 29 | 4010337832263 |
|  nero opaco | 2832 005 | 10 | 40,53 | 11 | 4010337038528 |
|  grigio opaco | 2832 015 | 10 | 40,53 | 11 | 4010337087120 |
|  acciaio inox (verniciato) | 2832 600 | 10 | 44,15 | 29 | 4010337022053 |

Caratteristiche

- Con morsetti a vite.

Dati tecnici

Profondità di montaggio: 25 mm

Sezione dei conduttori
- per conduttori fino a: 2,5mm²

Avvisi

- Solo per fissaggio a viti.
