








**Pulsante a bilanciere 3 moduli 10 A 250 V~ con bilanciere
Contatto di chiusura a 1 polo**



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2844 01	10	35,86	29	4010337082033
 bianco puro brillante	2844 03	10	35,86	29	4010337082040
 antracite	2844 28	10	38,46	29	4010337082064
 color alluminio	2844 26	10	42,29	29	4010337082057
 nero opaco	2844 005	10	42,29	29	4010337037903
 grigio opaco	2844 015	10	42,29	29	4010337087182
 acciaio inox (verniciato)	2844 600	10	45,92	29	4010337021957

Caratteristiche

- Con morsetti a vite.

Dati tecnici

Profondità di montaggio: 25 mm

Sezione dei conduttori
- per conduttori fino a: 2,5mm²

Avvisi

- Solo per fissaggio a viti.
