






**Interruttore a pulsante 10 AX 250 V~con bilanciere diritto 2 moduli  
Deviatore 2 moduli**

Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco puro brillante	2861 201	1/5	40,02	01	4010337065883
 bianco puro satinato	2861 27	1/5	40,02	01	4010337053286
 antracite	2861 28	1/5	40,54	11	4010337053293
 color alluminio	2861 26	1/5	43,74	11	4010337053279
 acciaio inox	2861 600	1/5	50,74	11	4010337021209

**Dati tecnici**

## Profondità di montaggio

- 2860 ...:	28 mm
- 2861 ...:	32 mm

## Sezione dei conduttori

- per conduttori rigidi e flessibili fino a:	2,5mm <sup>2</sup>
--	--------------------

## Potenza nominale

- LEDi/CFLi:	100 W
--------------	-------

**Avvisi**

- Soggetto a disponibilità.