








**Presse SCHUKO 16 A 250 V~ con scritta in rilievo "EDV"
System 55**

Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	4458 01	1/5	8,71	01	4010337093176
 bianco puro brillante	4458 03	1/5	8,71	01	4010337093190
 bianco puro satinato	4458 27	1/5	8,71	01	4010337093213
 antracite	4458 28	1/5	9,97	11	4010337093220
 color alluminio	4458 26	1/5	14,49	11	4010337093206
 nero opaco	4458 005	1/5	14,49	11	4010337093169
 grigio opaco	4458 015	1/5	14,49	11	4010337093183

Caratteristiche

- Anello portante con messa a terra.

Dati tecnici

Profondità di montaggio:	32 mm
Materiale conduttore:	rigido e flessibile
Sezione dei conduttori - per conduttori da:	da 1,5 mm ² a 2,5 mm ²

Avvisi

- Testato con pressione maggiore della staffa di terra secondo T.N.O.
