








Pulsante scrivibile System 106



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|--|-----------|----|-----------------------|----|---------------|
|  acciaio inox | 5549 920 | 1 | 51,00 | 20 | 4010337022800 |
|  alluminio | 5549 926 | 1 | 39,22 | 20 | 4010337022794 |
|  bianco traffico (verniciato) | 5549 902 | 1 | 34,43 | 20 | 4010337022787 |
|  acciaio inox V4A | 5549 914 | 1 | 69,08 | 20 | 4010337092056 |
|  bronzo | 5549 921 | 1 | 69,08 | 20 | 4010337100928 |
|  nero opaco | 5549 925 | 1 | 69,08 | 20 | 4010337100768 |

Avvisi

- Questo prodotto può essere ordinato esclusivamente tramite il servizio diciture Gira.
- Scritte professionali mediante il servizio diciture Gira www.beschriftung.gira.de.

Contenuto della fornitura

- Incl. dicitura stampata a laser personalizzata.

Dimensionin mm

H 25,3

B 105,5
