**Übersicht zur Integration von Modular Jack RJ 45-Buchsen in die Gira Schalterprogramme** PDF-Version

| Hersteller/Lieferant | Bezeichnung | Einsatz | Bestell-Nr. |
|---|---|---|---|
| METZ CONNECT (BTR) | 130 910 KI-E $C6_A$ Modul K Jack 180°<br>130 B22-E $C6_A$ Modul K180°<br>130 B22-E $C6_A$ Modul K270°<br>25Gmodul 130 B21-25-E | MJ-02 | 5602 00 |
| Telegärtner | AMJ Kupplung K 100023165<br>AMJ Kupplung K 100023227<br>AMJ Modul Cat.8.1 100023211<br>AMJ Modul K 100023173<br>AMJ Modul K 100023215<br>AMJ Modul K 100023225<br>AMJ Modul K 100023231<br>AMJ-S Modul 100023196<br>AMJ-S Modul 100023197<br>AMJ-S Modul 100023198<br>AMJ-S Modul 100023199<br>AMJ-S Modul 100023201<br>AMJ-S Modul 100023202<br>AMJ-S Modul 100023203<br>AMJ-S Modul 100023204<br>AMJ-S Modul 100023205<br>AMJ-S Modul 100023206<br>AMJ-SL Modul 100023207<br>AMJ-SL Modul 100023208<br>AMJ-SL Modul 100023209<br>AMJ-SL Modul 100023210 | MJ-02 | 5602 00 |
| AMP / TE Connectivity Ltd | AMP-TWIST Cat.$6_A$S SL Jack - 1711160-1 with dust cover, rear exit<br>AMP-TWIST Cat.$6_A$S SL Jack - 1711592-1 with dust cover<br>AMP-TWIST Cat.$6_A$S SL Jack - 1711716-1<br>AMP-TWIST Cat.6AS SL Jack DS12<br>AMP-TWIST Cat.6S SL Jack - 1711342-1 rear exit | MJ-03 | 5603 00 |
| METZ CONNECT (BTR) | BTR UAEMODUL 8(8) AANSL. | MJ-04 | 5604 00 |
| EFB-Elektronik | Cat.6 RJ45 Keystone, UTP, E-20081 | MJ-02 | 5602 00 |
| AMP / TE Connectivity Ltd | Cat.6 SL 110 Jack 568A/B, ALMOND - 1375055-1<br>Cat.6 SL Jack 568A/B geschirmt - 1375188-1 | MJ-03 | 5603 00 |
| EFB-Elektronik | Cat.6(A) RJ45 Keystone, E-20091 | MJ-08 | 5608 00 |
| SKM Skyline | Cat.6A CCS Easy Crimp Compact (Art.Nr. 125341) | MJ-04 | 5604 00 |
| EFB-Elektronik | Cat.6A RJ45 Keystone, UTP, E-20085 | MJ-08 | 5608 00 |
| DIGITUS | Cat.6A shielded, re-embedded Art.-Nr.: DN-93615 | MJ-04 | 5604 00 |
| CENTROVOX | CENTRONET Cat.6A-10G | MJ-04 | 5604 00 |
| SKM Skyline | Channel Klasse EA CCS Easy Crimp Compact (Art.Nr.125342) | MJ-04 | 5604 00 |
| Commscope (Gigaspeed, Powersom) | Commscope FDP-J5E RJ45 Cat.5E Modul<br>Commscope UNJ500 RJ45 Cat.5e Modul<br>Commscope UNJ600 RJ45 Cat.6 Modul | MJ-05 | 5605 00 |
| Diamond | DiaLink | MJ-08 | 5608 00 |
| DIGITUS | DIGITUS Professional Cat.6A shielded - EIA/TIA 568 A + B | MJ-04 | 5604 00 |

| | | | |
|---|---|---|---|
| 3M-Quante | DRIE M JACK UTP 5E WT ZK8 | MJ-01 | 5601 00 |
| eku Kabel & Systeme GmbH & Co. KG | E-Stone Pro Modul Cat.6A Art.-Nr.: t66850990 | MJ-04 | 5604 00 |
| ECOLAN | ECOLAN Cat.6A Keystone Gehäuse (Delta) Art.-Nr.: 99106036 | MJ-04 | 5604 00 |
| SKM Skyline | fixLink SL RJ45 Keystone Cat.6A (Art.Nr.130299) | MJ-04 | 5604 00 |
| Leoni Kerpen | GG 45 I06 BVSK und I11 BWSK | MJ-08 [1] | 5608 00 |
| Commscope (Gigaspeed, Powersom) | HGS620 RJ45 Cat.6A Modul Art.-Nr.: 760152801 | MJ-04 | 5604 00 |
| EFB-Elektronik | IKS-6A-KOP-12<br>IKS-6A-PVP-12 | MJ-08 | 5608 00 |
| Radiall | Jack Cat.6A Kupplung, geschirmt Art.Nr.:R280MOD832 | MJ-09 | 5609 00 |
| Komos | KDM 500 Cat.$6_A$ | MJ-02 | 5602 00 |
| DIGITUS | Keystone Cat.6 Art.-Nr.: DN-93614 | MJ-04 | 5604 00 |
| Hirschmann Multimedia B.V. | KS6A, 695020400 Data keystone CAT6A | MJ-02 | 5602 00 |
| Nexans | LANmark-5 EVO Snap-in-Buchse, geschirmt für AWG 24/1 - 22/1 - N420.555<br>LANmark-5 EVO Snap-in-Buchse, geschirmt für Litzenleiter AWG 26/7 - N420.556<br>LANmark-5 EVO Snap-in-Buchse, ungeschirmt für AWG 24/1 - 23/1 - N420.550<br>LANmark-5 EVO Snap-in-Buchse, ungeschirmt für AWG 27/7 - 26/7 - N420.551<br>LANmark-6 10G EVO Snap-in-Buchse, geschirmt - N420.666G<br>LANmark-6 10G EVO Snap-in-Buchse, geschirmt für Litzenleiter - N420.667G<br>LANmark-6 EVO RJ45 Snap-in Buchse, ungeschirmt für Litzenleiter AWG 26/7 - N420.661<br>LANmark-6 EVO RJ45 Snap-in-Buchse, geschirmt für AWG 24/1 - 22/1 - N420.666<br>LANmark-6 EVO RJ45 Snap-in-Buchse, geschirmt für Litzenleiter AWG 26/7 - N420.667<br>LANmark-6 EVO RJ45 Snap-in-Buchse, ungeschirmt für AWG 24/1 - 22/1 - N420.660<br>LANmark-$6_A$ Snap-in-Buchse Cat.6A 500MHz, geschirmt - N420.66A<br>LANmark-$6_A$ Snap-in-Buchse Cat.6A 500MHz, geschirmt für Litzenleiter - N420.67A | MJ-03 [2] | 5603 00 |
| | LANmark-7 GG45 Snap in Buchse für Litzenleiter Cat.7 - N420.731<br>LANmark-7 GG45 Snap-in- Buchse Cat.7 - N420.730<br>LANmark-7A GG45 12C Snap-in-Buchse Cat.7A 1000MHz geschirmt - N420.735<br>LANmark-7A GG45 12C Snap-in-Buchse Cat.7A 1000MHz geschirmt für Litzenleiter - N420.736 | MJ-08 [1] | 5608 00 |
| Legrand | LEGR Cat.5E UTP KEYSTONE<br>LEGR Cat.6 UTP KEYSTONE | MJ-09 | 5609 00 |
| LexCom | LexCom 125 STP, Cat.5E, RJ45<br>LexCom 125 UTP, Cat.5E, RJ45<br>LexCom 250 STP, Cat.6, RJ45<br>LexCom 250 UTP, Cat.6, RJ45<br>LexCom 500 STP, Cat.6A, RJ45 | - [3] | 5629 03 |
| AT & T | M11 B/C | MJ-05 | 5605 00 |
| Leoni Kerpen | MegaLine Connect 45 | MJ-04 | 5604 00 |
| Commscope (Gigaspeed, Powersom) | MGS500-262 RJ45 Cat.6A Modul Art.-Nr.: 760023614<br>MGS600-246 RJ45 Cat.6A Modul Art.-Nr.: 760092411<br>MGS600-262 RJ45 Cat.6A Modul Art.-Nr.: 760092429 | MJ-05 | 5605 00 |
| Lucent | MPS100 B/C (22DAS / A92/831/0051) | MJ-05 | 5605 00 |
| AVAYA | MPS100E RJ45 Cat.5e Modul | MJ-05 | 5605 00 |
| EFB-Elektronik | OC 45 Keystone, Class EA, E-20070 | MJ-08 | 5608 00 |

| | | | |
|---|---|---|---|
| | OC 45 Keystone, Class EA, E-20074 | | |
| METZ CONNECT (BTR) | OpDAT modul LC MM / Art.Nr. 150 910 75-I<br>OpDAT modul LC OM5 / Art.Nr. 150 910 7M-I<br>OpDAT modul LC-D MM / Art.Nr. 150 910 7B-I | MJ-02 | 5602 00 |
| Panduit | PAN CJ 5E LEAD FRAME IV. WIT<br>PAN CJ 5E LEAD FRAME WIT<br>PAN CJ 5E LEAD FRAME ZWART | MJ-06 | 5606 00 |
| | PAN CJ STP 6 TX<br>PAN CJ STP 6A 10G TG | MJ-10 | 5610 00 |
| | PAN CJ UTP 5E IWIT<br>PAN CJ UTP 5E TG IWIT<br>PAN CJ UTP 5E TG WT<br>PAN CJ UTP 5E TG ZW<br>PAN CJ UTP 5E WIT<br>PAN CJ UTP 5E WT<br>PAN CJ UTP 5E ZW<br>PAN CJ UTP 6 IWIT<br>PAN CJ UTP 6 TX aWT<br>PAN CJ UTP 6 TX WIT<br>PAN CJ UTP 6 WIT<br>PAN CJ UTP 6 ZWART<br>PAN CJ UTP 6 ZWART<br>PAN CJ UTP C6A 10G ZWART | MJ-06 | 5606 00 |
| | PAN KJ UTP 5 WIT<br>PAN KJ UTP 5 ZWART<br>PAN KJ UTP 5E IVOORWIT<br>PAN KJ UTP 5E WIT<br>PAN KJ UTP 6 WIT<br>PAN KJ UTP 6 ZWART | MJ-02 | 5602 00 |
| Harting | preLink RJ45 Keystone Cat.6 Art.-Nr.: 20825000001 | MJ-04 | 5604 00 |
| EasyLan | preLink RJ45 Keystone Cat.6A Art.-Nr.: CKPAO100 | MJ-04 | 5604 00 |
| RadiaII | RADI MJ STP 6A<br>RADI MJ UTP 5<br>RADI MJ UTP 6<br>RADI MJ UTP 6 | MJ-04 | 5604 00 |
| TKM | RJ-MOD - Cat.6 geschirmt<br>RJ-MOD - Cat.6A | MJ-04 | 5604 00 |
| inLine | RJ45 Bu/LSA Einsatz, Snap-In, Cat.6a | MJ-04 | 5604 00 |
| CobiNet | RJ45 Buchse CobiDat KS TPS 500 Cat.6A Art.-Nr.: 6920 4050 | MJ-03 | 5603 00 |
| eLANTIX (Ficonet) | RJ45 Cat.6A 10G Modul Art.-Nr.: EX-MJC6AS | MJ-04 | 5604 00 |
| R&M | RJ45 Cat.6A EL Anschlussmodul, geschirmt mit Keystoneadapter / R-Nr. R813512<br>RJ45 Cat.6A EL Anschlussmodul, ungeschirmt mit Keystoneadapter / R-Nr. R813514<br>RJ45 Cat.6A ISO Anschlussmodul, geschirmt mit Keystoneadapter / R-Nr. R509509<br>RJ45 Cat.6A ISO Anschlussmodul, ungeschirmt mit Keystoneadapter / R-Nr. R509508 | MJ-08 | 5608 00 |
| RDUN (Rheinland Daten- und Netzwerktechnik oHG) | RJ45 Modul geschirmt Cat.6A/EA Art.-Nr.: 90254311500 | MJ-04 | 5604 00 |
| CobiNet | RJ45-Buchse KS ICS 250 MHz Cat.6 gemäß ISO/IEC 11801, Art.Nr. 6920 0022.1<br>RJ45-Buchse KS ICS 500 MHz Cat.$6_A$ ISO/IEC 11801-3:2017, GHMT PVP-zertifiziert, Art.Nr. 6920 0052/P.1<br>RJ45-Buchse KS ICS 500 MHz Cat.6A ISO/IEC 11801-3:2017, Art.Nr. 6920 0052.1<br>RJ45-Buchse KS IPS 250 MHz Cat.E PL gemäß ISO/IEC 11801, Art.Nr. 6920 1022.1<br>RJ45-Buchse KS IPS 500 MHz Klasse $E_A$, PL gemäß ISO/IEC 11801-3:2017, Art.Nr. 6920 1052.1 | MJ-04 | 5604 00 |
| | RJ45-Buchse KS IPU 100 MHz Cat.5e UTP gemäß ISO/IEC 11801, Art.Nr. 6920 0120 | MJ-08 | 5608 00 |

| | | | |
|---|---|---|---|
| | RJ45-Buchse KS IPU 250 MHz Cat.6 UTP gemäß ISO/IEC 11801, Art.Nr. 6920 0110 | | |
| Telegärtner | RJ45-Keystone 90° 100023179 | MJ-02 | 5602 00 |
| CobiNet | RJ45-Kupplung KS IPS 250 MHz Cat.E PL gemäß ISO/IEC 11801, Art.Nr. 6925 1052.1 | MJ-04 | 5604 00 |
| Corning | S500 Keystone Cat.6A, CAXBSM-00104-C001 mit Staubschutz | MJ-08 | 5608 00 |
| AMP / TE Connectivity Ltd | SL JACK FTP 5E 1375189-1<br>SL JACK UTP 5E 1375191-2<br>SL JACK UTP 6 1375055-2 | MJ-03 | 5603 00 |
| Systimax | Systimax 360 ™ 10G MGS 600 RJ45 Cat.6A Modul<br>Systimax M1AH RJ45 M-Series UTP USOC<br>Systimax M1BH-H RJ45 Cat.3 Modul<br>Systimax MGS 400 RJ45 Cat.6 Gigaspeed | MJ-05 | 5605 00 |
| AT & T | T568 B | MJ-05 | 5605 00 |
| Brandrex | Tollfree Cat.$6_A$ Jack Art.-Nr.: AC6JAKS0000DC<br>Toolfree Cat.6 Jack UTP568 (A/B wired) Art.-Nr.: C6CJAKU002 | MJ-02 | 5602 00 |
| Schrack | Toolless Buchse RJ45 UTP Cat.5 / HSEMRJ5UWS | MJ-04 | 5604 00 |
| AMP / TE Connectivity Ltd | Toolless Cat.3 RJ11 Jack - 1116603-2<br>Toolless Cat.5E RJ45 Jack - 1116604-2<br>Toolless Cat.5E RJ45 shielded Jack - 1339015-1 | MJ-03 | 5603 00 |
| Radiall | Toolless Jack Cat.5e Art.-Nr.: R280MOD807<br>Toolless Jack Cat.6 Art.-Nr.: R280MOD803A | MJ-04 | 5604 00 |
| | Toolless Jack Cat.6, unshield, Art.Nr.: R280MOD834 | MJ-08 | 5608 00 |
| | Toolless Jack Cat.6A Art.-Nr.: R280MOD810 shield<br>Toolless Jack Cat.6A STP Art.-Nr.: R280MOD831<br>Toolless Jack KJ15 Series Cat.6 Art.-Nr.: R280MOD800 | MJ-04 | 5604 00 |
| Schrack | Toolless Line Buchse RJ45 geschirmt Cat.6 (SFB) / HSEMRJ6GBS<br>Toolless Line Buchse RJ45 geschirmt Cat.$6_A$ (SFB) HSEMRJ6GBA | MJ-04 | 5604 00 |
| | Toolless Line Buchse RJ45 STP 10GB / Klasse $E_A$ / HSEMRJ6GWT<br>Toolless Line Buchse RJ45 STP Cat.5e / HSEMRJ5GWS | MJ-08 | 5608 00 |
| | Toolless Line Buchse RJ45 STP Cat.6 / Klasse E / HSEMRJ6GWS | MJ-04 | 5604 00 |
| | Toolless Line Buchse RJ45 STP Cat.$6_A$ / HSEMRJ66GWA<br>Toolless Line Buchse RJ45 UTP Cat.6 re-embedded / HSEMRJ6UWS | MJ-08 | 5608 00 |
| Setec | UKJ RJ45 Cat.6, geschirmt Art.-Nr.: 501292 | MJ-04 | 5604 00 |
| Rutenbeck | UM Cat.6A ISO A 13900304<br>UM-real. Cat.6 U A 13700300 | MJ-04 | 5604 00 |
| Telegärtner | UMJ Kupplung K 100023168<br>UMJ Kupplung K 100023229<br>UMJ Modul K 100023226<br>UMJ Modul K 100023230<br>UMJ Modul K 100023232<br>UMJ Modul K 100023235 | MJ-02 | 5602 00 |
| Dätwyler | unilan® RJ45 Modul KS-T Plus 1/8 Cat.6A (IEC) - 418 061 | MJ-04 | 5604 00 |
| | unilan® Modul KS-T 1/8 Toolless Cat.6/EA geschirmt - 418 053<br>unilan® Modul KS-T 6A 1/8 Toolless Cat.6A/EA geschirmt - 418 060<br>unilan® Modul KS-T5 1/8 Toolless Cat.5e geschirmt - 418 055 | MJ-08 | 5608 00 |
| | unilan® Modul PS-GG45 7A 1000 MHz 4P Two-in-One geschirmt - 400 102<br>unilan® Modul PS-GG45 7A 1000 MHz 4P Two-in-One geschirmt für Litzen - 400 103 | MJ-08 [1] | 5608 00 |
| | unilan® RJ45 Modul KU-T 1/8 Cat.5e ungeschirmt, toolless - 418 072 / 073 | MJ-04 | 5604 00 |

| | | | |
|---|---|---|---|
| | unilan® RJ45 Modul KU-T 1/8 Cat.6 ungeschirmt, toolless- 418 070 / 071<br>unilan® RJ45 Modul MS-K Plus 1/8 Cat.$6_A$ (IEC) - 440 004 | | |
| Radiall | UTP Toolless Jack Cat.6A Art.-Nr.: R280MOD830 unshielded | MJ-04 | 5604 00 |
| 3M-Quante | Volition Cat.6A PL 180 Anschlussmodul TypNr.: 05-753-21200<br>Volition K6 Anschlussmodul STP, einzelgeschirmt TypNr.: 43096-746 00 | MJ-01 | 5601 00 |
| Setec | XKJ RJ45 Cat.6/6A geschirmt Art.-Nr.: 501378 und 501379 | MJ-04 | 5604 00 |

[1] Requires Keystone Clip (metal) - N429.620

[2] Requires Keystone Clip (blue) - N429.626

[3] Installation in cover 5629.. / Lexcom mounting frame required