






**Drukcontact 10 A 250 V~ met rechtstaande wip met controlevenster**  
**Wisselcontact 1-polig**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit glanzend	0120 201	1/5	20,63	11	4010337065982
 zuiver wit mat	0120 27	1/5	20,63	01	4010337029465
 antraciet	0120 28	1/5	21,37	11	4010337029489
 kleur aluminium	0120 26	1/5	24,57	11	4010337029472
 zwart mat	0120 005	1/5	24,57	11	4010337037927
 edelstaal	0120 600	1/5	31,34	11	4010337021247

**Technische gegevens**

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm <sup>2</sup>

**Aanwijzingen**

- Ook verlichtbaar aan te sluiten.