






Drukcontact 10 A 250 V~ met rechtstaande wip met controlevenster
Wisselcontact 1-polig



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|--|----------|-----|--------------------|----|---------------|
|  zuiver wit glanzend | 0120 201 | 1/5 | 20,63 | 11 | 4010337065982 |
|  zuiver wit mat | 0120 27 | 1/5 | 20,63 | 01 | 4010337029465 |
|  antraciet | 0120 28 | 1/5 | 21,37 | 11 | 4010337029489 |
|  kleur aluminium | 0120 26 | 1/5 | 24,57 | 11 | 4010337029472 |
|  zwart mat | 0120 005 | 1/5 | 24,57 | 11 | 4010337037927 |
|  edelstaal | 0120 600 | 1/5 | 31,34 | 11 | 4010337021247 |

Technische gegevens

| | |
|---|--------------------|
| Inbouwdiepte: | 28 mm |
| Aansluitingdoorsnede - voor stijve en flexibele geleiders tot: | 2.5mm ² |

Aanwijzingen

- Ook verlichtbaar aan te sluiten.

- Volgens beschikbaarheid.
