








**Tastschakelaar 10 AX 250 V~met rechtstaande wip
Universele uit-wisselschakelaar**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 zuiver wit glanzend	0121 201	1/5	17,70	01	4010337052692
 zuiver wit mat	0121 27	1/5	17,70	01	4010337029311
 antraciet	0121 28	1/5	18,20	11	4010337029335
 kleur aluminium	0121 26	1	21,40	11	4010337029328
 zwart mat	0121 005	1	21,40	11	4010337037972
 grijs mat	0121 015	1	21,40	11	4010337077091
 edelstaal	0121 600	1/5	28,42	11	4010337021261

Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele geleiders tot:	2.5mm ²
Nominaal vermogen - LEDi/ CFLi:	100 W

Aanwijzingen

- Volgens beschikbaarheid.
