








**Tast-controleschakelaar 10 AX 250 V~ met wip  
Schakelaar 2-polig**



| Specificatie  | Art. nr. | VE  | EUR/stuk excl. BTW | PS | EAN           |
|---|----------|-----|--------------------|----|---------------|
|  crème wit glanzend   | 0122 01  | 1/5 | 45,00              | 01 | 4010337122012 |
|  zuiver wit glanzend | 0122 03  | 1/5 | 45,00              | 01 | 4010337122036 |
|  zuiver wit mat      | 0122 27  | 1/5 | 45,00              | 01 | 4010337122272 |
|  antraciet           | 0122 28  | 1/5 | 45,55              | 11 | 4010337122289 |
|  kleur aluminium     | 0122 26  | 1/5 | 48,71              | 11 | 4010337122265 |
|  zwart mat           | 0122 005 | 1/5 | 48,71              | 11 | 4010337037934 |
|  edelstaal           | 0122 600 | 1/5 | 55,78              | 11 | 4010337021773 |

**Technische gegevens**

|   |                    |
|---|--------------------|
| Inbouwdiepte:   | 28 mm              |
| Aansluitingdoorsnede<br>- voor stijve en flexibele geleiders tot: | 2.5mm <sup>2</sup> |
| Nominaal vermogen<br>- LEDi/ CFLi:                                | 100 W              |

---

## Aanwijzingen

- Ook verlichtbaar aan te sluiten.
- Volgens beschikbaarheid.

---

## Levering

- Glimlampelement 230 V~, 1,5 mA is bij de levering inbegrepen.
-