











**Tastchakelaar 10 AX 250 V~ met wip**  
**Universele uit-wisselschakelaar**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0126 01	1/5	16,95	01	4010337126010
 zuiver wit glanzend	0126 03	10	16,95	01	4010337126034
 zuiver wit mat	0126 27	10	16,95	01	4010337126270
 antraciet	0126 28	10	17,43	11	4010337126287
 kleur aluminium	0126 26	1/5	20,50	11	4010337126263
 zwart mat	0126 005	10	20,50	11	4010337037965
 grijs mat	0126 015	1/5	20,50	11	4010337077145
 edelstaal	0126 600	1/5	27,22	11	4010337021742
 brons	0126 603	1/5	26,94	11	4010337106043

## Technische gegevens

Inbouwdiepte:	28 mm
Aansluitingdoorsnede - voor stijve en flexibele leidingen tot:	2,5 mm <sup>2</sup>
Nominaal vermogen - LEDi/ CFLi:	100 W

---