









**Tastschakelaar 10 AX 250 V~ met wip**  
**Universele uit-wisselschakelaar**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0126 01	1/5	17,70	01	4010337126010
 zuiver wit glanzend	0126 03	1/5	17,70	01	4010337126034
 zuiver wit mat	0126 27	1/5	17,70	01	4010337126270
 antraciet	0126 28	1/5	18,20	11	4010337126287
 kleur aluminium	0126 26	1/5	21,40	11	4010337126263
 zwart mat	0126 005	1/5	21,40	11	4010337037965
 grijs mat	0126 015	1/5	21,40	11	4010337077145
 edelstaal	0126 600	1/5	28,42	11	4010337021742

**Technische gegevens**

Inbouwdiepte: 28 mm

Aansluitingdoorsnede  
- voor stijve en flexibele geleiders tot: 2.5mm<sup>2</sup>

Afbeeldingen zijn gelijkend en kunnen van het origineel afwijken.  
Prijzen geldig voor België met prijzen per 01/24.

Nominaal vermogen

- LEDi/ CFLi:

100 W

---

## Aanwijzingen

- Volgens beschikbaarheid.

---