








Ruimtetemperatuurregelaar 24/5 (2) A~ met wisselcontact



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0397 01	1/5	104,48	02	4010337397014
 zuiver wit glanzend	0397 03	1/5	104,48	02	4010337397038
 zuiver wit mat	0397 27	1/5	104,48	02	4010337397274
 antraciet	0397 28	1/5	107,26	02	4010337397281
 kleur aluminium	0397 26	1/5	111,51	02	4010337397267
 zwart mat	0397 005	1/5	111,51	02	4010337037446

Technische gegevens

Nominale spanning:	AC 24 V
Nominale stroom	
- Verwarmen (verbreekcontact):	10 (4) A
- Koelen (maakcontact):	5 (2) A
Aansluitvermogen	
- Verwarmen (verbreekcontact):	ca. 240 W
- Koelen (maakcontact):	ca. 120 W
Schakeltemperatuurverschil:	ca. 0,5 K
Energieklasse:	I = 1 %

Inbouwdiepte:	25 mm
Omgevingstemperatuur:	+5 °C tot +30 °C

Aanwijzingen

- Alleen voor schroefbevestiging.
 - Vlakke uitvoering.
-