







## Wandcontactdoos stereo-luidspreker



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	0402 01	1/5	18,71	01	4010337402015
 zuiver wit glanzend	0402 03	1/5	18,71	01	4010337402039
 zuiver wit mat	0402 27	1/5	18,71	01	4010337402275
 antraciet	0402 28	1/5	21,31	11	4010337402282
 kleur aluminium	0402 26	1/5	23,96	11	4010337402268
 zwart mat	0402 005	1/5	23,96	11	4010337037880

### Kenmerken

- Met schroefklemmen.

### Technische gegevens

Inbouwdiepte: 31 mm  
Aansluitingdoorsnede max.: 1.5mm<sup>2</sup>

## Aanwijzingen

- Voor kabeldoorsnede tot max. 10 mm<sup>2</sup>.
  - Te gebruiken voor high-end luidsprekerconnectors (WBT) en datakap.
-