







Wandcontactdoos stereo-luidspreker



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|----------|-----|--------------------|----|---------------|
|  crème wit glanzend | 0402 01 | 1/5 | 18,71 | 01 | 4010337402015 |
|  zuiver wit glanzend | 0402 03 | 1/5 | 18,71 | 01 | 4010337402039 |
|  zuiver wit mat | 0402 27 | 1/5 | 18,71 | 01 | 4010337402275 |
|  antraciet | 0402 28 | 1/5 | 21,31 | 11 | 4010337402282 |
|  kleur aluminium | 0402 26 | 1/5 | 23,96 | 11 | 4010337402268 |
|  zwart mat | 0402 005 | 1/5 | 23,96 | 11 | 4010337037880 |

Kenmerken

- Met schroefklemmen.

Technische gegevens

Inbouwdiepte: 31 mm
Aansluitingdoorsnede max.: 1.5mm²

Aanwijzingen

- Voor kabeldoorsnede tot max. 10 mm².
 - Te gebruiken voor high-end luidsprekerconnectors (WBT) en datakap.
-