








**Dubbele wandcontactdoos met randaarde 16 A 250 V~ met verhoogde aanraakbeveiliging (Safety Plus) en vaste afdekplaat voor inbouwapparaatdoos 1-voudig**



| Specificatie  | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN           |
|---|----------|----|--------------------|----|---------------|
|  crème wit glanzend   | 0783 01  | 1  | 22,05              | 01 | 4010337783015 |
|  zuiver wit glanzend | 0783 03  | 1  | 22,05              | 01 | 4010337783039 |
|  zuiver wit mat      | 0783 27  | 1  | 22,05              | 01 | 4010337783275 |
|  antraciet           | 0783 28  | 1  | 24,66              | 11 | 4010337783282 |
|  kleur aluminium     | 0783 26  | 1  | 28,63              | 11 | 4010337783268 |
|  zwart mat           | 0783 005 | 1  | 28,63              | 11 | 4010337037507 |
|  grijs mat           | 0783 015 | 1  | 28,63              | 11 | 4010337081876 |

## Technische gegevens

|   |   |
|---|---|
| Inbouwdiepte:   | 25 mm                                       |
| Aansluitingdoorsnede<br>- voor geleiders van:           | 1,5 mm <sup>2</sup> tot 2,5 mm <sup>2</sup> |
| Omgevingstemperatuur<br>- verhoogde aanraakbeveiliging: | 0 °C tot +45 °C                             |

---

## Aanwijzingen

- Passend in alle gangbare apparaatdozen.
  - Verhoogde aanraakbeveiliging (Safety Plus) conform IEC 60884-1.
-