

## Wipschakelaar 10 AX 250 V~ met wip 2-voudig voor weergave hotelkamerstatus



| Specificatie                                                                                            | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN           |
|---------------------------------------------------------------------------------------------------------|----------|----|--------------------|----|---------------|
|  crème wit glanzend    | 1104 01  | 1  | 38,47              | 01 | 4010337104018 |
|  zuiver wit glanzend | 1104 03  | 1  | 38,47              | 01 | 4010337104032 |
|  zuiver wit mat      | 1104 27  | 1  | 38,47              | 01 | 4010337104278 |
|  antraciet           | 1104 28  | 1  | 38,95              | 11 | 4010337104285 |
|  kleur aluminium     | 1104 26  | 1  | 42,13              | 11 | 4010337104261 |
|  zwart mat           | 1104 005 | 1  | 42,13              | 11 | 4010337038535 |

### Kenmerken

- Schakelaar voor weergave hotelkamerstatus "Do not disturb" en "Make up room".
- Met vergrendeling tegen dubbelzijdig inschakelen.
- Elektrisch en mechanisch vergrendeld.

### Technische gegevens

|                                                                   |                    |
|-------------------------------------------------------------------|--------------------|
| Inbouwdiepte:                                                     | 28 mm              |
| Aansluitingdoorsnede<br>- voor stijve en flexibele geleiders tot: | 2.5mm <sup>2</sup> |

Nominaal vermogen

- LEDi/ CFLi:

100 W

---

## Aanwijzingen

- Volgens beschikbaarheid.

---