









Thermostaat met drukcontactinterface 4-voudig voor KNX



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2100 01	1	353,15	06	4010337048022
 zuiver wit glanzend	2100 03	1	353,15	06	4010337048039
 zuiver wit mat	2100 27	1	353,15	06	4010337048060
 antraciet	2100 28	1	355,79	06	4010337048077
 kleur aluminium	2100 26	1	360,07	06	4010337048053
 zwart mat	2100 005	1	360,07	06	4010337037255
 grijs mat	2100 015	1	360,07	06	4010337083016
 edelstaal	2100 600	1	367,60	06	4010337021520

Kenmerken

- Met de instelwiel wordt de temperatuurinstelwaarde verschoven.
- Een aanwezigheidstoets is bedoeld om te schakelen tussen de comfortstand en stand-bymodus.
- De huidige toestanden worden op de thermostaat met leds weergegeven.

Technische gegevens

Inbouwdiepte: 23 mm
