











Wippenset 3-voudig



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend (gelakt)	2183 01	1	30,26	06	4010337012146
 zuiver wit glanzend (gelakt)	2183 03	1	30,26	06	4010337012153
 zuiver wit mat (gelakt)	2183 27	1	30,26	06	4010337013389
 antraciet (gelakt)	2183 28	1	34,33	06	4010337012160
 aluminiumkleurig (gelakt)	2183 26	1	37,36	06	4010337012177
 zwart mat (gelakt)	2183 005	1	37,36	06	4010337038382
 grijs mat (gelakt)	2183 015	1	37,36	06	4010337083177
 edelstaal	2133 601	1	25,11	06	4010337020196
 brons	2133 605	1	24,38	06	4010337083399

Aanwijzingen

- Beschrijfbare wippensets en wippensets zonder tekstkader zijn van metaal, dit kan bij draadloze toepassingen het bereik beperken.
